

## Mask E 80-S plus

Professional masking tape for the automotive and car body repair industries; suitable for applications that require resistance to high temperatures (up to 80 °C for 1 hour / up to 100 °C for 20 minutes). Natural rubber adhesive with plasticizing, antioxidant and solvent resins.



### ADVANTAGES AND PERFORMANCES

- Good adhesiveness on irregular surfaces
- Residue-free removal
- Saturated paper for maximum conformability
- Compatible with the most common paints
- Removable without tearing
- High tack cross-linked adhesive

### TECHNICAL PROPERTIES

		tolerance	test method
Backing:	100 µm saturated white paper		
Adhesive:	natural rubber and plasticizing, antioxidant and solvent resins		
Total thickness:	125 µm	± 10 %	AFERA 5006
Adhesion to steel:	min. 2,2 N/cm		AFERA 5001
Tensile strength:	min. 28 N/cm		AFERA 5004
Elongation at break:	min. 7 %		AFERA 5004
Temperature resistance:	up to 80 °C for 1 h / up to 100 °C for 20 min		
Colour:	white and yellow		

The above values are the result of arithmetic averages from tests on sample productions and are not legally binding.

### ARTICLES, DIMENSIONS AND BARCODES

	dimensions	pieces per box	barcode
Mask E 80-S plus white:	19 mm x 50 m	96 rolls	8051499031923
Mask E 80-S plus white:	25 mm x 50 m	72 rolls	8051499031930
Mask E 80-S plus white:	30 mm x 50 m	60 rolls	8051499031947
Mask E 80-S plus white:	38 mm x 50 m	48 rolls	8051499031954
Mask E 80-S plus white:	50 mm x 50 m	36 rolls	8051499031961
Mask E 80-S plus yellow:	19 mm x 50 m	96 rolls	8051499032142
Mask E 80-S plus yellow:	25 mm x 50 m	72 rolls	8051499032159
Mask E 80-S plus yellow:	30 mm x 50 m	60 rolls	8051499032166
Mask E 80-S plus yellow:	38 mm x 50 m	48 rolls	8051499032173
Mask E 80-S plus yellow:	50 mm x 50 m	36 rolls	8051499032180

### OUR PROPOSAL OF PACKAGING

- Sleeve with B/W or coloured (up to 5 colours) barcode label
- Harmonica

### RECOMMENDATIONS

It's a good rule to use the product within 6 months from purchase, because the unwinding force of the tape increases with time. The product must be stored in its box in a dry location protected from sunlight, at about 15 °C - 25 °C and 50% relative humidity. If stored in different conditions, the product must be reconditioned. After application, the removal of the tape must be done slowly without tears. Before applying the tape, always check if the surface is clean. Euromask disclaims any liability for any direct or indirect damage coming from the misuse of the product. Under normal conditions, the tape is not toxic and is not approved for medical use.

The a.m. values may be changed at any moment for production needs or technical updates.

rev. 01\_May 2019